

Bed & Chair



1 ADJUSTABLE BACK REST

HEMOCRAFT

This back rest can be adjusted by a simple ratchet mechanism. Height of back 570mm (22 1/2"). Width 500mm (19 3/4"). Depth of base 390mm (15 1/2"). Weight 2.2kg. Maximum user weight AA3612

AA3612

2 ADJUSTABLE BED CRADLE

HEMOCRAFT

A simple metal frame, whose base slips between the mattress and the bed base. The top forms a support cradle for the bedclothes to keep them clear of the feet and legs. The height is adjusted easily. The frame is in two parts for easy storage or transport. For use at the side or end of the bed. Height 454 to 680mm (18 to 27"). Width 356mm (14"). Length: Top 565mm (22 1/2"); Base 710mm (28"). Weight 3kg.

AA3652



3 ROPE LADDER BED HOIST

HEMOCRAFT

A simple idea to assist with sitting up in bed. The bottom ends of the cords tie around the bed legs, and the plastic ladder rungs can be gripped to pull the user up in bed on a hand over hand movement. Suitable for single or double beds. Rung length 200mm (8"). Diameter 25mm (1"). Cord length 3 metres (9'10"). Weight 285g.

AA3660

4 COMMUNITY BED PAD

This bed pad is warm and comfortable but highly absorbent. It keeps the sleeper dry, reduces bed changes and helps prevent soreness and infection. Quilted with highly absorbent fibres for faster dispersal of liquid and durable waterproof backing. Machine washable. Size 700 x 850mm (27 1/2 x 33 1/2"). Absorbency 2 litres.

AA2734

5 POSITIONING WEDGE

Eliminates the need for makeshift rolls to safely maintain the individual in proper position. Soft, washable outer fabric cover, with enclosed zipper, encapsulates the polystyrene bead filling to provide support, adjustability and comfort for the user.

C829803 Large, 430 x 200 x 200mm

C829804 X-Long, 635 x 200 x 200mm

A81245 Replacement polystyrene beads; 1 cu. foot



6 EASY CUSHION

A versatile U-shaped cushion that can be used to give support and comfort to various parts of the body. It can be used on the floor or in a bed to lift the head and neck when reading or it can be wrapped round the waist when sitting to give the back support. Alternatively, it can be used between legs to help keep hips in alignment, or to help keep the user in a particular position, eg. the recovery position. Also useful in bed to keep the body stable and provide comfort. Optional washable blue cover.

AA4005 Easy Cushion

AA4005A Easy Cushion Cover



1 HOMECRAFT BED GRAB RAIL

An ultra sturdy bed grab rail, offering stability and confidence to those that have difficulty getting into and out of bed. The height adjustable frame can be positioned to suit virtually any divan style bed. Two legs rest upon the floor and the frame is secured into place via the three colour coded straps provided, ensuring minimal movement when in use. Supplied flat packed, the Homecraft bed grab rail is simple to assemble and fit. Height of handle 850 to 950mm (33 1/2 to 37 1/2") from the floor. Width of handle at the top 265mm (10 1/2"). Size of under mattress frame 620 x 325mm (24 1/2 x 12 3/4"). Weight 3.5kg.

AA3475


Maximum user weight 127kg.



2 EASYLEAVER™ BED RAIL

This device enables the user to pull themselves from a lying position to a seated position when in bed. It also provides support when standing or entering and leaving the bed, thus helping to promote independence within the bedroom. May be used with most beds and cannot be felt through a standard depth mattress. Easy to assemble and supplied with fixing straps for extra security. Suitable for single to king size beds. Width 365mm (14 3/8"). Length 620mm (24 1/2"). Handle height 470mm (18 1/2"). Weight 3.1kg. Maximum user weight 108kg.

AA3470



3 STACKABLE CONE RAISERS

HEMOCRAFT

Lightweight but extremely strong moulded cones with a broad base and a recess for the chair or bed leg. They have anti-slip pads to hold castors still. Sold in sets of four. Maximum total load 222kg.

Spares are available, making this product suitable for refurbishment.

	Height	Weight
AA3302	140mm (5 1/2")	145g each

4 WOODEN CHAIR RAISERS

A lacquered hardwood cube with three 16mm (5/8") recesses of different diameters, to suit different leg widths. Blox height 111mm (4 3/8"). Height raise 75mm (3"). Max diameter of leg 30, 50 or 75mm (1 1/4, 2 or 3"). Weight 425g each, 1.7kg set of 4. Supplied as set of 4. Maximum total load 190kg.


AA3306



5 WOODEN BED RAISERS

A lacquered hardwood cube, with one recess in the top and an additional plywood base for greater stability. Designed specifically for beds. Block height 178mm (7"). Raise 130mm (5"). Max leg diameter 75mm (3"). Base 152mm (6") square. Weight 750g each, 3kg set of 4. Supplied as set of 4. Maximum total load 318kg.

AA3308



Dressing & Grooming



1 DRESSING STICK

HEMOCRAFT

This wooden stick with rubber tip at one end and special double wire hook at the other, is used to pull on or push off garments that cannot be reached easily e.g. socks. Length 520mm (21"). Weight 236g.

AA4680

2 DRESS EZ DRESSING STICK

Combines two functions in one aid – a dressing stick and a shoehorn. One end has a strong plastic, push-pull S-hook that retrieves clothing or other items. The other end is a long-handled shoehorn. The thick, easy-to-hold shaft has a foam covering to improve grip. 610mm (24") long.

2102

3 COMPRESSION STOCKING AID

ROLYAN

A stocking aid which will apply support hosiery quickly and evenly. Grooves catch the compression stocking and prevent it from popping off. Works like a traditional sock aid - just pull the stocking over the shell, insert the foot and pull the cord to bring the hose up onto the leg. Suitable for Class 1 and 2 stockings. Recommended for below knee stockings but may still be suitable for some above knee models.

Small - 130mm wide x 140mm high

Large - 150mm wide x 145mm high

Weight

A75440 Small 960g

A75441 Large 980g



4 SOCK NOTCH™

ROLYAN

Ideal for people who have the use of only one hand or with decreased strength or coordination. The notch in the side of aid helps to hold the sock or stocking in place whilst it is applied to the aid. The cord style helps apply shorter socks; the garter style helps apply longer stockings that go over the calf. The garter style also features a handle that is ideal for people with a limited grasp. May be appropriate following stroke, head injury or spinal cord injury and for people with arthritis. Flexible plastic.

A754200 Cord style

A754300 Garter style

5 TERRY CLOTH SOCK AID

Sock application is made easy with this flexible, plastic sock aid. Slits in the plastic core allow it to bend around the heel. The inside is lined with nylon to reduce friction. The outside is lined with terry cloth to hold the sock firmly until it is on the foot. Two pulling tabs with loop handles permit one-handed application. Washable. Length 230mm (9"). Weight 73g.

A7273




1 DORKING STOCKING AID HOMECRAFT

A simple, inexpensive device to assist with putting on stocking or sock. It consists of a strong, shaped, flexible plastic gutter with long cotton tapes attached to the top. The stocking or sock is fed on to the plastic and held in place with the side notches. The foot is put in the open end of the stocking, which is then pulled over the foot and up the leg using the tapes. Cord length 920mm (36"). Gutter length 229mm (9"). Weight 55g.

AA4650Y Standard


AA4652Y Side Slot



2 DORKING TIGHTS AID HOMECRAFT

This works on the same principle as the stocking aid above, but has a double gutter to enable it to be used for tights. Cord length 920mm (36"). Length 229mm (9"). Weight 106g.


AA4654Y



3 BREVETTI SOCK & STOCKING AID HOMECRAFT

This device is particularly useful to aid putting on socks, but can also be used for stockings. It consists of a plastic collar or gutter for holding the garment at one end and a plastic shoehorn with a notch for easy sock removal at the other. The two are connected by a coated steel tube. Length 737mm (29"). Weight 386g.

AA4666



4 EZ SLIDE SHOEHORN

This specially coated shoehorn prevents the metal shaft from sticking to either the skin or clothing. The shaft has fewer curves than normal shoehorns improving the insertion and removal of the foot. The handle is made from a non-slip material.


A7152 Length 610mm



5 PLASTIC SHOE HORN HOMECRAFT

An inexpensive plastic moulded shoehorn. A long handle gives excellent reach. It also has a hanging loop attached to the handle. Length 430mm (17"). Weight 37g.


AA4600Y



6 METAL SHOE HORN HOMECRAFT

A sturdy long white epoxy coated steel shoehorn for easier reaching. The soft PVC handgrip is hook-shaped for hanging and hooking. Length 600mm (24"). Weight 233g.

AA4606Y



Dressing & Grooming



1 SOESI ELASTIC LACES

HEMOCRAFT

These look like normal shoe laces with crimped ends, but are elasticated and effectively convert lace-up shoes into slip-on shoes, for those who have trouble reaching or tying shoe laces.

	Length	Colour	Qty	Weight
AA4612C	450mm (18")	Brown	3 pairs	14g
AA4612GW	450mm (18")	Black	3 pairs	14g
AA4616C	610mm (24")	Brown	2 pairs	10g
AA4616G	610mm (24")	Black	2 pairs	10g



2 KINGS BUTTON HOOK

HEMOCRAFT

A shaped stainless steel wire which assists one handed dressing by passing through the button hole and over the button to grip the thread. It is pulled through with a twisting motion. Length: Wire 97mm (33/4"), Handle 120mm (43/4").

AA4677



3 LONG HANDLED COMBS & BRUSH

These utensils assist those who cannot raise their arm or reach behind their head to comb their hair. They consist of a lightweight moulded plastic handle with a push-on extension piece, a hinged end piece which holds the comb or brush and has two different angled positions. When not in use, the comb or brush folds back into the handle and the extension can be taken off to give a pocket sized item. Length: With extension 460mm (18"); With handle 320mm (12 1/2"). Length folded 235mm (9 1/4").

		Weight
AA4710W	Fine comb	120g
AA4712	Style comb	114g
AA4714	Brush	128g



4 HANDS FREE HAIRDRYER STAND

A convenient stand that holds the hairdryer steady for one handed styling or drying. The hairdryer nestles securely in a foam padded clamp on top of a flexible neck that can be adjusted to any angle from its tabletop base. Useful for hemiplegics, arthritics and others with limited upper extremity range of motion, strength or co-ordination.

This simple, but essential piece of equipment increases independence for user or carer.

C6475

5 NAIL CARE COMBINATION SET

This two-in-one aid for fingernail care is designed for people who cannot grasp or use small hand-held implements. Mounted onto a plastic base with non-slip feet, the stainless steel trimmer clips nails with a simple push of the lever. An emery board is held rigidly in a spring clip for one-handed filing. Two emery boards included.

AA4737